





SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			



37P	55.42	63.50	69.32	8.38	12.50
25P	38.96	47.04	53.04	8.38	12.50
15P	25.25	33.32	39.14	8.38	12.50
9P	16.92	24.99	30.81	8.38	12.50
POS. NO.	A	B	C	D	E

DIMENSION




SPECIFICATIONS:

- Current rating: 3.0A AC/DC
- Voltage rating: 250V AC/DC
- Contact resistance: 30m ohm MAX
- Insulation resistance: 5000M ohm MIN
- Withstanding voltage: 1000V AC for one minute
- Operating temperature range: -40° C ~ +85° C

MATERIAL AND FINISH

- Insulator: PBT+30%G.F(UL94V-0)
- Contact: Copper Alloy Nickel Undercoated
- Selective Gold Plated
- Finish: Metal Iron With Tin Plated

Ordering Information



JHJM 深圳市君灏精密工业有限公司
ShenZhen JunHao Exactitude Industry CO.,LTD

PART. NAME: D型双芯焊线式PCB焊接插座~针~				TITLE:	
PART. NO.: SUB-DBAM-102A-092				DWG NAME:	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
Jonsson	Jeff	allan	Jacky		± 0.50
					± 0.30
					± 0.10
					± 1°
				UNITS: mm	
				SCALE:	
				REVISION:	