

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ


X2026 W V X-2*XX A -XX SN XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-Straight 180°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: 2*XX-2*02P~2*20P
- ⑥ Plug the Pin & Special No.:
A- With Lock on both side
- ⑦ Material: 6T-PA6T 94V-0; N0-PA66 94V-0
- ⑧ Plating Category: SN-Bright Tin Plating
- ⑨ Color : Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*2	2.00	8.00	2*14	26.00	32.00
2*3	4.00	10.00	2*15	28.00	34.00
2*4	6.00	12.00	2*16	30.00	36.00
2*5	8.00	14.00	2*17	32.00	38.00
2*6	10.00	16.00	2*18	34.00	40.00
2*7	12.00	18.00	2*19	36.00	42.00
2*8	14.00	20.00	2*20	38.00	44.00
2*9	16.00	22.00	2*21	40.00	46.00
2*10	18.00	24.00	2*22	42.00	48.00
2*11	20.00	26.00	2*23	44.00	50.00
2*12	22.00	28.00	2*24	46.00	52.00
2*13	24.00	30.00	2*25	48.00	54.00

X2026WV-2*XXA-6TSN	PA6T UL 94V-0	Brass	Tin-Plated	X2026H-A
X2026WV-2*XXA-N0SN	PA66 UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal



For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

Authorized Signature(s)

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X2026WV-2*XXA-XXSN
CHKD	DATE	UNIT: mm	PART NO.:
APPD	DATE	SIZE: A4	2.00mm Crimp Style Connectors
			DWG NO.:
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	

XKB INDUSTRIAL PRECISION CO., LIMITED