



| PANEL CUT-OUT |             |           |
|---------------|-------------|-----------|
| Z             | Y           | X         |
| 0.70~1.25     | 13.50~13.70 | 28.9~29.1 |
| 1.25~2.00     | 13.50~13.70 | 29.1~29.2 |
| 2.00~3.00     | 13.50~13.70 | 29.2~29.3 |

NOTES:

- Rating:  
KC 16(4)A 250V AC T85/55  
VDE ENEC 16(4)A 250V AC T85/55  
CCC 16(4)A 250V AC T105/55  
UL cUL 16GPA 125V AC/16GPA 250V AC T105/55
- Circuit Diagram: 3P ON-OFF
- Terminal Strength: ≥80N
- Electrical life: ≥10000 cycles
- Withstand Voltage: Withstand Voltage: 1500VAC 1min  
Terminals to Button: 3000VAC 1min  
Leakage Current: 1mA
- Current resistance: ≤50mΩ (initial)
- Insulation resistance: ≥100MΩ
- Body Material: NYLON 66 94V-0-2



普通公差:  
COMMON TOLERANCE:

|      |      |                      |
|------|------|----------------------|
| A4   |      |                      |
| A3   |      |                      |
| A2   |      |                      |
| A1   |      |                      |
| REV. | DATE | REVISION DESCRIPTION |
|      |      | ISSUE                |

# 深圳市华灿天禄电子有限公司

|               |       |      |            |     |     |     |         |                    |    |      |
|---------------|-------|------|------------|-----|-----|-----|---------|--------------------|----|------|
| UP TO 5       | ±0.20 | 单位   | mm         | 投影  | 核 对 | 吴路方 | 品 名     | 跷板开关               | 比例 | Free |
| ABOVE 5 TO 30 | ±0.30 | 绘 图  | 周金勇        | 核 对 | 核 准 | 周培雷 | 型 号     | RS606              |    |      |
| ABOVE 30      | ±0.50 | DATE | 2016.01.07 | 核 准 |     |     | 图 号     | RS606A-1011N012BRB |    |      |
| ANGULAR       | ±5°   |      |            |     |     |     | DWG NO. |                    |    |      |