



PS-22E05XX

PUSH SWITCH

G-Switch P/N


N=NO LOCK
L=LOCK

A=黑色
B=红色
C=蓝色
D=其它



G-Switch Specification:
 Electrical Specifications: 0.5A 30VDC
 Contact Resistance: $\leq 100m\Omega$
 Insulation Resistance: $\geq 100M\Omega$ DC125V
 Withstand Voltage: AC125V 1 minute
 Operating Temperature: -25°C~+65°C
 Storage Humidity: $\leq 85\%RH$
 Electrical Life: 10 000
 Mechanical Life: 100 000

注：“*”表示关键尺寸(7个)



RoHS
Compliant
2002/95/EC



Unless otherwise specified, Tolerance:
 X ±0.30
 X.X ±0.20
 X.XX ±0.15
 X.XXX ±0.10
 Angles ±3

G-Switch Electronic (HongKong) CO.,Ltd.

DESIGN Bright Lee DATE 2016.05.29 Mold code:

CHECKED DATE APPROVED DATE

APPROVED DATE

http://www.dg-switch.com

TEL:0769-82388879

PS-22E05

REV.: X1 SCALE: 4:1 UNIT: mm

SIZE: A4 SHEET: 1/1