

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS


Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

SS320F	UNITS
200	V
140	V
200	V
3.0	A
80	A
0.92	V
0.05	mA
10	mA
250	PF
10	°C/W
-65 -+ 150	°C
-65-+150	°C

NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2. Thermal Resistance Junction to Lead Vertical PC Board Mounting 0.5"(12.7mm) Lead Length.



RATING AND CHARACTERISTIC CURVES (SS315F THRU SS320F)

www.gk-goodwork.com.