



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤30mΩ
- After environmental testing: ≤50mΩ

X2026 H X-2*XX D-N0 XX

- ① Series No.
- ② Category: H-HSG
- ③ Appearance type: Blank-Ordinary
- ④ Row No.-Pin No.: 2*XX-2*02P~2*22P
- ⑤ Plug the Pin & special No.:
D-With Lock in the middle
- ⑥ Material: N0-PA66 94V-0
- ⑦ Color: Blank-Natural Color

| Poles | Dimensions (mm) | | | Poles | Dimensions (mm) | | |
|-------|-----------------|-------|-------|-------|-----------------|-------|-------|
| | A | B | C | | A | B | C |
| 2*02 | 2.00 | 4.60 | 6.76 | 2*12 | 22.00 | 24.60 | 26.76 |
| 2*03 | 4.00 | 6.60 | 8.76 | 2*13 | 24.00 | 26.60 | 28.76 |
| 2*04 | 6.00 | 8.60 | 10.76 | 2*14 | 26.00 | 28.60 | 30.76 |
| 2*05 | 8.00 | 10.60 | 12.76 | 2*15 | 28.00 | 30.60 | 32.76 |
| 2*06 | 10.00 | 12.60 | 14.76 | 2*16 | 30.00 | 32.60 | 34.76 |
| 2*07 | 12.00 | 14.60 | 16.76 | 2*17 | 32.00 | 34.60 | 36.76 |
| 2*08 | 14.00 | 16.60 | 18.76 | 2*18 | 34.00 | 36.60 | 38.76 |
| 2*09 | 16.00 | 18.60 | 20.76 | 2*19 | 36.00 | 38.60 | 40.76 |
| 2*10 | 18.00 | 20.60 | 22.76 | 2*20 | 38.00 | 40.60 | 42.76 |
| 2*11 | 20.00 | 22.60 | 24.76 | | | | |

| | | | |
|-----------------|-------------------|-----------------------|-----------------------|
| X2026H-2*XXD-N0 | Nylon 66 UL 94V-0 | X2026T-D | X2026W-D |
| PART NO | Material | Suitable XKB Terminal | Suitable XKB Terminal |

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

| | | | | | | | | | | | |
|------|-------------------------|------|---------|----------|------------------------|--|------|------------|--------------------------------|--------------|----------------|
| △ X | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES | DSND | DATE | SCALE: N/A | MODEL TYPE: X2026H-2*XXD-N0 | | |
| △ X | | | | | | DWN | DATE | VIEW: | PART NO.: | | |
| △ X | | | | | | CHKD | DATE | UNIT: mm | 2.00mm Crimp Style Connectors | | |
| MARK | | | | | | APPD | DATE | SIZE: A4 | DWG NO.: | | |
| | Authorized Signature(s) | | | | | XKB INDUSTRIAL PRECISION CO., LIMITED | | | WEIGHT 1.0g | SHEET 1/1 | REVISION A0 |

