



SPECIFICATION

Poles: 2-24
 Voltage rating: AC, DC 250V
 Current rating: AC, DC, 7A
 Withstand voltage: 1500V AC min.
 Insulation resistance: 1000MΩ min.
 Temperature range: -25℃ ~ +85℃
 Applicable PC board thickness: 0.031" ~ 0.063"
 (0.8 ~ 1.6mm)
 Contact resistance: Initial value 10mΩ max.
 After environmental testing 20mΩ max.
 Material: Nylon66 UL94V-2
 Contact: Brass
 Finish: Tin-plated
 Color: Nature

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	CLIENT P/N / 5557S-2*XP 空心针
CHECKED:	DATE:	
DRAWN:	DATE:	UNIT mm SCALE free FILE NO. Ckmtw-5557-0005
LYF	2008-04-07	

深圳市灿科盟实业有限公司
CHANKLEMENT INDUSTRY CO., LTD

