



	MYLAR	1		Black
	HOUSING	1	HIGH TEMP.THERMOPLASTIC	Black
	TERMINAL 7#	1	COPPER ALLOY t=0.20	Au-Plated
	TERMINAL 6#	1	COPPER ALLOY t=0.20	Au-Plated
	TERMINAL 5#	1	COPPER ALLOY t=0.20	Au-Plated
	TERMINAL 4#	1	COPPER ALLOY t=0.20	Au-Plated
	SHELL	1	SUS301 t=0.20	Ni-Plated
	TERMINAL 2#	1	COPPER ALLOY t=0.20	Au-Plated
	TERMINAL 1#	1	COPPER ALLOY t=0.20	Au-Plated
NO.	PART NAME	QTY	MATERIAL(THICK)	PLATING(COLOR)

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					X.X ±0.2mm
Δx					X.XX ±0.1mm
					X.XXX ±0.05mm

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.5PHONE JACK
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	DWG NO.:
APPD		DATE		SIZE: A4	PJ-3566D
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET
				1.0g	1/1
				REVISION	A0