



## Specification

Insulator Material: Polysetc, UL94V-0

Standard: Nylon-6T

Contact Material: Brass

Contact plated: Gold Over Nickel

Current Rating : 1Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40 °C -- +105 °C

APPROVED:	DATE:	<b>C</b> 深圳市灿科盟实业有限公司 KIM T W CHAN KHEUNG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 210-1S-2*5P L=5.8MM (3.0/1.0/1.8)			
DRAWN:	DATE:	CLIENT P/N	SCALE	REV.	
LXF	2008-04-29	C2895038	free	⊕	A
TOLERANCE TABLE		UNIT	mm	SCALE	free
	.0				
	.00				
	.000				
	±0.20				
	±0.10				
	±0.05				

PCB LAYOUT