







**技术参数 SPECIFICATIONS**  
 间距 (Pitch) : 0.5  
 极数 (Poles) : 4~60  
 额定电压 (Voltage rating): 50V DC/AC  
 额定电流 (Current rating) : 0.5A DC/AC  
 耐压值 (Withstand Voltage) : 500V  
 工作温度 (Working Temperature) : -25°C ~ +85°C  
 绝缘电阻 (Insulation Resistance) : ≥ 500MΩ  
 接触电阻 (Contact resistance) : ≤ 30mΩ  
 单面接触 (Single contact)

**材料 Material**  
 接触件 (Contact) : 磷青铜 t=0.2mm 镀互焊  
 焊片 (solder tab) : 磷青铜 t=0.2mm 镀互焊  
 塑胶主体 (Housing) : LCP 耐热树脂 (UL94V-0) Heat resistance plastic (UL94V-0)  
 滑动架 (Slider) : PPS 耐热树脂 (UL94V-0) Heat resistance plastic (UL94V-0)



【数据37~80】

【数据4~36】

规格 A	B	C	
04	1.50	2.6	8.1
05	2.00	3.1	8.6
06	2.50	3.6	9.1
07	3.00	4.1	9.6
08	3.50	4.6	10.1
09	4.00	5.1	10.6
10	4.50	5.6	11.1
11	5.00	6.1	11.6
12	5.50	6.6	12.1
13	6.00	7.1	12.6
14	6.50	7.6	13.1
15	7.00	8.1	13.6
16	7.50	8.6	14.1
17	8.00	9.1	14.6
18	8.50	9.6	15.1
19	9.00	10.1	15.6
20	9.50	10.6	16.1
21	10.00	11.1	16.6
22	10.50	11.6	17.1
23	11.00	12.1	17.6
24	11.50	12.6	18.1
25	12.00	13.1	18.6
26	12.50	13.6	19.1
27	13.00	14.1	19.6
28	13.50	14.6	20.1
29	14.00	15.1	20.6
30	14.50	15.6	21.1
31	15.00	16.1	21.6
32	15.50	16.6	22.1
33	16.00	17.1	22.6
34	16.50	17.6	23.1
35	17.00	18.1	23.6
36	17.50	18.6	24.1
37	18.00	19.1	24.6
38	18.50	19.6	25.1
39	19.00	20.1	25.6
40	19.50	20.6	26.1
41	20.00	21.1	26.6
42	20.50	21.6	27.1
43	21.00	22.1	27.6
44	21.50	22.6	28.1
45	22.00	23.1	28.6
46	22.50	23.6	29.1
47	23.00	24.1	29.6
48	23.50	24.6	30.1
49	24.00	25.1	30.6
50	24.50	25.6	31.1
51	25.00	26.1	31.6
52	25.50	26.6	32.1
53	26.00	27.1	32.6
54	26.50	27.6	33.1
55	27.00	28.1	33.6
56	27.50	28.6	34.1
57	28.00	29.1	34.6
58	28.50	29.6	35.1
59	29.00	30.1	35.6
60	29.50	30.6	36.1

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	CHECKED:	DATE:	DRAWN:	DATE:
				hh-H	2019-01-02
TITLE:		PART. NO.			
FPC0.5-XP 上接 抽拉式		/			
UNIT	mm	SCALE	free	REV.	A LY00
FILE NO.	Ckmtw-FPC-0094				

**深圳市灿科盟实业有限公司**  
**CKMTW CHANKLEMENT INDUSTRY CO., LTD**