



RECOMMENDED P.C.B LAYOUT

Specification

Insulator Material: Polyeser, UL94V-0

Standard: P.B.T

Contact Material: Brass

Contact plated: Gold Over Nickel

Poles: 2~40P

Current Rating : 3Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40℃ -- +105℃

未注公差表

X.X	±0.2
X.XX	±0.10
X.XXX	±0.050

核准:

日期:

业务:

日期:

制图:

日期:

L.Y.F

2013-2-22

深圳市灿科盟实业有限公司
CHANKLEMENT INDUSTRYCO., LTD

品名规格:

210R-1*3P 空中间P L=13.8MM

客户料号 C2895036

单位	mm	比例	/	版本	A
----	----	----	---	----	---

图纸编号: S051400078