


2

3


B

С



D

Ε



Materials HOUSING: P.P.S. ACTUATOR: PA66 MOVABLE CONTACT: Tin bronze, silver plated.

Specifications

CONTACT RATING: 0.1A @ 30 VDC. min. @ 100 VDC. MECHANICAL & ELECTRICAL LIFE: 50,000 cycles. CONTACT RESISTANCE: 150 m Ω max. initial. INSULATION RESISTANCE: 100 M Ω OPERATING TEMPERATURE: -20°C to +70°C. DIELECTRIC STRENGTH: 100 volts AC @ 60 Hz. PACKAGING: Bulk.

-

				_	-								_	
A4									UNIT	ММ	PROJECTED	♦₽	PRODUCT N	AME:
A3							COMMON 1	OLERANCE:	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:	DDB001
A2					台	普	X.XX	± 0.10	DATE	2017	APPROVAL BY	ALEN	Https:	www.rocpu.tw
A1					ROCI	PU	X.X X	<u>± 0.15</u> ± 0.25	ROC	; PU	TECHN		ONGY	COITD
REV.	DATE	REVISION DESCRIPTION ISS		ISSUE	Е	F	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A B					C			D		Е		F	G