

SPECIFICATION:

1. Material

Housing Material:High temperature thermoplastic
 Contact Terminal:High Grade Copper Alloy
 Merallic Shell:Stainless Steel
 Inner Ground Cover Shell:Stainless Steel
 Mid Plate:Stainless Steel

2. Mechanical:

2.1.Mating force:5-20Nf;
 2.2.Unmating force:Initial:8-20Nf;Final:6-20Nf;
 2.3.Durability:5000 Cycles;


3. Electrical:

3.1.Current Rating:3A
 3.2.Voltage Rating:20V Max.;
 3.3.Dielectric Withstanding
 volage:100Vac,60S,10mA;
 3.4.Contact resistance:40m Ohms Max.;

4. Environmental:

4.1.Operating temperature:-40°C~+85°C;
 4.2.Salt Spray Test:24H Min.(No oxidation or rust);

U262-16XN-4BC20865



					DSND		DATE		SCALE: N/A	MODEL TYPE: 3.1 TYPE C		
					DWN		DATE		VIEW:	PART NO.:		
					CHKD		DATE		UNIT: mm/in	DWG NO.:		
					APPD		DATE		SIZE: A4	U262-16XN-4BC20865		
					UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION
					KXB INDUSTRIAL PRECISION CO.,LIMITED					1.0g	1/1	A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	REVISIONS
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
MARK					L > 63 ±0.5