

Product Specification Sales Drawing

This document was generated on 06/22/2021 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0512160500</u>			
Status:	Active		lan 2	
Overview:				
Description:				1
Documents:				7140
3D Model		Product Specification PS-51216-007-001 (PDF)	5 A	
Drawing (PDF)		Packaging Specification SPK-51216-001-001 (PDF)		1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
<u>3D Model (PDF)</u>		RoHS Certificate of Compliance (PDF)		
	n PS-51216-006-001 (PDF)			
	<u>11 3-31210-000-001 (1 D1)</u>		Series image	e - Reference only
Agonov Cortificatio	2			
Agency Certificatio	n	E29179	EU ELV	
UL			Not Relevant	
General				
Product Family		Crimp Housings	EU RoHS	China RoHS
Series		51216	Compliant	
Application		Signal, Wire-to-Board, Wire-to-Wire	REACH SVHC	
Overview		MicroTPA Connector System	Not Contained Per -	
Product Name		MicroTPA	D(2020)9139-DC (1	
UPC		800754824378	Jan 2021)	-
			Halogen-Free	
Physical			Status	
Circuits (maximum)		5	Not Low-Halogen	
Color - Resin		Natural		n, please visit <u>Contact US</u>
Gender		Receptacle		n, ploade view <u>contact co</u>
Glow-Wire Capable		No	China ROHS	Green Image
Lock to Mating Part		Yes	ELV	Not Relevant
Material - Resin		Polyester	RoHS Phthalates	Not Contained
Net Weight		281.900/mg	,	
Number of Rows		1		
Packaging Type		Bag	Search Parts in t	his Sarias
Panel Mount		No	<u>51216</u> Series	
Pitch - Mating Interfa	ice	2.00mm		
Stackable		No		
Temperature Range	- Operating	-40° to +105°C	Mates With	
Material Info		<u>51227</u> , <u>55755</u> , <u>5</u>	5487	
Reference - Drawing Numbers			Use With	
Packaging Specifica		SPK-51216-001-001	<u>59370</u> , <u>51217-05</u>	<u>05</u>
			1	

This document was generated on 06/22/2021

PS-51216-006-001, PS-51216-007-001

SD-51216-004-001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION