

ROCPU Product features Voltage: < 5V Current: < 20mA Conduction time: 2ms Closed circuit resistance: < 100hm Open circuit resistance: > 20m ohm High temperature resistance:120 ℃/260 ℃ Terminal tension: 1000gf / min Humidity: 25~95%RH Working lifespan:20,000 cycles Error rate:1%

G

ROCPU Product features

1. TPSW-200D is a dual ball single direction tilt inductive trigger switch.

2. When the guide end (no pin end) of the product is inclined and the inclination angle is greater than 10 degrees, the product is in open circuit, (off) state; when the product is horizontal and the inclination angle is greater than 10 degrees, the product is in closed circuit (On) state.ROCPU

3. When it is placed horizontally, shaking is easy to trigger, but when there is no foot down, shaking is not easy to trigger.ROCPU

4. The product of this specification is completely sealed, waterproof and

5. Under normal conditions, the service life of the switch can reach 100000 times. 6. This product is environmentally friendly.ROCPU

6	Plug	1	PC		
5	Ball	1	Brass	SC	
4	Ball	1	Brass	SC&GP2U	
3	Pin A	1	Brass	SILVERING	
2	Pin B	1	Brass	GP 2U	
1	Copper Pipe	1	Brass	SC&GP2U	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING	REMARK

A4						COMMON TOLERANCE:	UNIT	ММ	PROJECTED	♦₽	PRODUCT N	AME:	
A3					台普	COMMON	OLERANCE:	DRAWN BY	FUYUAN	CHECKED BY	coco	MODEL NO:	TPSW-200D-G
⁵ А2						X.XX	± 0.10	DATE	2017	APPROVAL BY	ALEN	Https:	www.rocpu.tw
A1					ROCPL		± 0.15 ± 0.25	ROC	PU	TECHN		NGY	COITD
REV.	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR	ANGULAR Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus v						
	AB				C		D		E		F	G	