


**P.C.B. LAYOUT  
BOTTOM VIEW**




**SCHEMATIC (SHOTRING)**

**SS-23E03-GXXX**

直柄 G-Switch P/N

- G=020 (2.0)    G=030 (3.0)
- G=040 (4.0)    G=050 (5.0)
- G=055 (5.5)    G=060 (6.0)
- G=065 (6.5)    G=070 (7.0)
- G=075 (7.5)    G=080 (8.0)
- G=085 (8.5)    G=090 (9.0)
- G=095 (9.5)    G=100 (10.0)

G-Switch Specification:  
 RATING (额定值) : DC250V 0.5A  
 CONTACT RESISTANCE 接触电阻:  $\leq 70m\Omega$   
 INSULATION RESISTANCE 绝缘电阻:  $\geq 100m\Omega$   
 DIELECTRIC STRENGTH 耐电压: AC 500V for 1 minute  
 TIMING (时间特性) : SHORTING



**G-Switch Electronic Technology CO.,Ltd.**

Unless otherwise specified, Tolerance:  
 X.  $\pm 0.30$   
 X.x  $\pm 0.20$   
 X.xx  $\pm 0.15$   
 X.xxx  $\pm 0.10$   
 Angles  $\pm 3'$

DESIGN	陈锋枫	DATE	2016.05.29
CHECKED		DATE	
APPROVED		DATE	
<a href="http://www.dg-switch.com">http://www.dg-switch.com</a>		REV.:	X1
TEL:0769-82388879		SCALE:	4:1
		UNIT:	mm
		SIZE:	A4
		SHEET:	1/1

TITLE:  
**SS-23E03-GXXX**

