





SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			



37P	55.42	63.50	69.32	8.38	12.50
25P	38.96	47.04	53.04	8.38	12.50
15P	25.25	33.32	39.14	8.38	12.50
9P	16.92	24.99	30.81	8.38	12.50
POS. NO.	A	B	C	D	E

DIMENSION




### SPECIFICATIONS:

Current rating:3.0A AC/DC  
Voltage rating:250V AC/DC  
Contact resistance:30m ohm MAX  
Insulation resistance:5000M ohm MIN  
Withstanding voltage:1000V AC for one minute  
Operating temperature range:-40° C~+85° C

### MATERIAL AND FINISH

Insulator:PBT+30%G.F(UL94V-0)  
Contact:Copper Alloy Nickel Undercoated  
Selective Gold Plated  
Finish:Metal Iron With Tin Plated

## Ordering Information



**JHJM** 深圳市君灏精密工业有限公司  
ShenZhen JunHao Exactitude Industry CO.,LTD

PART. NAME: D型双芯焊线式PCB焊接插座~针~				TITLE:	
PART. NO.: SUB-DBBF-107A-092				DWG NAME:	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
Jonsson	Jeff	allan	Jacky		± 0.50
				UNITS: mm	± 0.30
				SCALE:	± 0.10
				REVISION:	± 1°