



△			
△			
△			

SPECIFICATIONS:
 Current rating:3.0A AC/DC
 Voltage rating:250V AC/DC
 Contact resistance:30m ohm MAX
 Insulation resistance:5000M ohm MIN
 Withstanding voltage:1000V AC for one minute
 Operating temperature range:-40°C~+85°C

MATERIAL AND FINISH
 Insulator:PBT+30%G.F(UL94V-0)
 Contact:Copper Alloy Nickel Undercoated
 Selective Gold Plated
 Finish:Metal Iron With Tin Plated

Ordering Information

SUB — DRXX — X0XX — XXX

Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Definition
A	9 PIN	M	Male	6	SCREWED HEX SCREW ON BOARD LOCK	2	Brass	A	Gold 1u"/Light Tin	0	PBT	0	Black
B	15 PIN	F	Female	7	RIVETED W/ BOARD LOCK/WASHER	7	Phosphor bronze	B	Gold 3u"/Light Tin	2	NYLON	6	Blue
C	25 PIN			8	RIVETED W/BOARD LOCK/ WASHER/HEX SCREW			C	Gold 5u"/Light Tin			9	White
E	37 PIN			9	RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW			E	Gold 15u"/Light Tin				
								F	Gold 30u"/Light Tin				

JHJM 深圳市君灏精密工业有限公司
 ShenZhen JunHao Exactitude Industry CO.,LTD

PART. NAME: D型XX芯弯式PCB焊接插座(孔)				TITLE:			
PART. NO.: SUB-DRAM-602A-002				DWG NAME:			
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance		
Jonsson	Jeff	allan	Jacky		UNITS: mm	x.	±0.50
					SCALE:	x.x	±0.30
					REVISION:	x.xx	±0.10
						xx'	±1"