



Δ			
Δ			
Δ			

SPECIFICATIONS:
 Current rating: 3.0A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 30m ohm MAX
 Insulation resistance: 5000M ohm MIN
 Withstanding voltage: 1000V AC for one minute
 Operating temperature range: -40°C ~ +85°C

MATERIAL AND FINISH
 Insulator: PBT+30%G.F(UL94V-0)
 Contact: Copper Alloy Nickel Undercoated
 Selective Gold Plated
 Finish: Metal Iron With Tin Plated

Ordering Information

SUB		DRXX		X0XX		XXX			
Number of contacts	Housing Type	Mounting Options		Contacts Material	Contact Plated	Insulator material	Insulator color	Mark	
Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Definition
A	9 PIN	6	SCREWED HEX SCREW ON BOARD LOCK	2	Brass	A	Gold 1u"/Light Tin	0	PBT
B	15 PIN	7	RIVETED W/ BOARD LOCK/WASHER	7	Phosphor bronze	B	Gold 3u"/Light Tin	2	NYLON
C	25 PIN	8	RIVETED W/BOARD LOCK/WASHER/HEX SCREW			C	Gold 5u"/Light Tin	6	Black
E	37 PIN	9	RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW			E	Gold 15u"/Light Tin	9	White
						F	Gold 30u"/Light Tin		

POS. NO.	A	B	C	X	Y
37P	54.83	63.50	69.32	8.08	9.50
25P	38.38	47.04	53.04	8.08	9.50
15P	24.66	33.32	39.14	8.08	9.50

JHJM 深圳市君灏精密工业有限公司
ShenZhen JunHao Exactitude Industry CO.,LTD

PART. NAME: D型XX芯弯式PCB焊接插座(孔)				TITLE:	
PART. NO.: SUB-DRBM-602A-002				DWG NAME:	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
Jonsson	Jeff	allan	Jacky		x. ±0.50
					x.x ±0.30
					x.xx ±0.10
					xx' ±1"