

△			
△			
△			

**SPECIFICATIONS:**  
 Current rating:3.0A AC/DC  
 Voltage rating:250V AC/DC  
 Contact resistance:30m ohm MAX  
 Insulation resistance:5000M ohm MIN  
 Withstanding voltage:1000V AC for one minute  
 Operating temperature range:-40°C~+85°C

**MATERIAL AND FINISH**  
 Insulator:PBT+30%G.F(UL94V-0)  
 Contact:Copper Alloy Nickel Undercoated  
 Selective Gold Plated  
 Finish:Metal Iron With Tin Plated


## Ordering Information

SUB — DRXX — X0XX — XXX

Number of contacts	Housing Type	Mounting Options	Contacts Material	Contact Plated	Insulator material	Insulator color	Mark
Code Definition	Code Definition	Code Definition	Code Definition	Code Definition	Code Definition	Code Definition	Code Definition
A 9 PIN	M Male	6 SCREWED HEX SCREW ON BOARD LOCK	2 Brass	A Gold 1u"/Light Tin	0 PBT	0 Black	0 NONE
B 15 PIN	F Female	7 RIVETED W/ BOARD LOCK/WASHER	7 Phosphor bronze	B Gold 3u"/Light Tin	2 NYLON	6 Blue	2 Nextron
C 25 PIN		8 RIVETED W/BOARD LOCK/WASHER/HEX SCREW		C Gold 5u"/Light Tin		9 White	
E 37 PIN		9 RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW		E Gold 15u"/Light Tin			
				F Gold 30u"/Light Tin			

POS. NO.	A	B	C	X	Y
37P	54.83	63.50	69.32	8.08	9.50
25P	38.38	47.04	53.04	8.08	9.50
15P	24.66	33.32	39.14	8.08	9.50
9P	16.33	24.99	30.81	8.08	9.50

DIMENSION



**JHJM 深圳市君灏精密工业有限公司**  
 ShenZhen JunHao Exactitude Industry CO.,LTD

PART. NAME: D型XX芯弯式PCB焊接插座(孔)				TITLE:	
PART. NO.: SUB-DRCF-607A-002			DWG NAME:		
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
Jonsson	Jeff	allan	Jacky		x. ±0.50
				UNITS: mm	x.x ±0.30
				SCALE:	x.xx ±0.10
				REVISION:	xx' ±1"