


Δ			
Δ			
Δ			

**SPECIFICATIONS:**  
 Current rating:3.0A AC/DC  
 Voltage rating:250V AC/DC  
 Contact resistance:30m ohm MAX  
 Insulation resistance:5000M ohm MIN  
 Withstanding voltage:1000V AC for one minute  
 Operating temperature range:-40°C~+85°C

**MATERIAL AND FINISH**  
 Insulator:PBT+30%G.F(UL94V-0)  
 Contact:Copper Alloy Nickel Undercoated  
 Selective Gold Plated  
 Finish:Metal Iron With Tin Plated

## Ordering Information

SUB		DRXX		X0XX		XXX		
Number of contacts	Housing Type	Mounting Options		Contacts Material	Contact Plated	Insulator material	Insulator color	Mark
Code Definition	Code Definition	Code	Definition	Code Definition	Code Contact Area	Code Definition	Code Definition	Code Definition
A 9 PIN	M Male	6	SCREWED HEX SCREW ON BOARD LOCK	2	Brass	0	PBT	0
B 15 PIN	F Female	7	RIVETED W/ BOARD LOCK/WASHER	7	Phosphor bronze	B	NYLON	6
C 25 PIN		8	RIVETED W/BOARD LOCK/WASHER/HEX SCREW			C		9
E 37 PIN		9	RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW			E		
						F		



**JHJM 深圳市君灏精密工业有限公司**  
**ShenZhen JunHao Exactitude Industry CO.,LTD**

PART. NAME: D型XX芯弯式PCB焊接插座(孔)				TITLE:			
PART. NO.: SUB-DRCM-602A-002				DWG NAME:			
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance		
Jonnson	Jeff	allan	Jacky		x.	±0.50	
					x.x	±0.30	
					x.xx	±0.10	
					xx'	±1"	