



P.C.B LAYOUT  
XKB Connectivity

XKB Connectivity

■ 规格 Specifications:

- 额定电压 Voltage rating:250VAC/DC.
- 额定电流 Current rating:3A AC/DC
- 耐电压 Withstanding voltage:1000V AC/minute
- 温度区间 Temperature range:-40℃to+105℃
- 绝缘电阻 Insulation resistance:≥1000MΩ Min
- 接触电阻 Contact resistance:≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 波峰焊温度 Wave soldering temperature:255±5℃,10s

XKB Connectivity

X4621 F V - 2\*XX - C43 D28  
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category:F-Female
- ③ Welding Board Angle:V-Stright 180°
- ④ Row No -Pin No:2\*XX-2\*01P-40P
- ⑤ Plastic height: C=4.3mm
- ⑥ Plastic length:D=2.8mm

XKB Connectivity

X4621FV-2*XX-C43D28	PA6T 94V-0	Brass	1U"Gold	X4621W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期  
發 日期

文件工程章  
REVISIONS

www.xkb.cn www.hellixkb.com www.hellixkb.cn

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X4621FV-2*XX-C43D28
DWNN	DATE	VIEW: ④	PART NO.: 2.00mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0