



Recommended P.C.B  
Layout(±0.05)

Technical Data

Pin(outer sleeve):Brass,machined CuZn38Pb2

Insulator:PPS UL94V-0 colour:black

Current rating:3Amps

Mating pin Ø:0.60mm

Contact resistance:max 10mΩ

Dielectric strength:min 1000V RMS

Operating temperature:-40°C to+105°C

Soldering temperature:+255°C

X5511W V- XX -C396 D43-1220

- ①
- ②
- ③
- ④
- ⑤
- ⑥
- ⑦

- ① Series.NO.
- ② Category : W-Wafer
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:XX-01P-XXP
- ⑤ Pin Length :C=3.96mm
- ⑥ Pin Length :D=4.3mm
- ⑦ 1220:Type1220

X5511WV-XX-C396D43-1220	PPS 94V-0	Brass	Tin Gold 1µ"	X5511F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

广东星坤科技股份有限公司

生 日期

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

DSND	DATE	SCALE: N/A	MODEL TYPE: X5511WV-XX-C396D43-1220
DWVN	DATE	VIEW: ④	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

REVISIONS  
DATE REVISED APPROVED

www.xkb.cc.cn www.hellixkb.com www.hellixkb.cn