






| Poles | Dimensions(mm)<br>A |
|-------|---------------------|
| 2*02  | 5.08                |
| 2*03  | 7.62                |
| 2*04  | 10.16               |
| 2*05  | 12.70               |
| 2*06  | 15.24               |
| 2*07  | 17.78               |
| 2*08  | 20.32               |
| 2*09  | 22.86               |
| 2*10  | 25.40               |
| 2*12  | 30.48               |
| 2*14  | 35.56               |
| 2*16  | 40.64               |
| 2*20  | 50.80               |
| 2*21  | 53.34               |
| 2*24  | 60.96               |
| 2*25  | 63.50               |



Recommended P.C.B  
Layout(±0.05)

Technical Data  
Pin(outer sleeve):Brass,machined CuZn38Pb2  
Insulator:PPS UL94V-0 colour:black  
Current rating:3Amps  
Mating pin Ø:0.60/0.48mm  
Mechanical life:min 500cycles  
Contact resistance:max 10m Ω  
Dielectric strength:min 1000V RMS  
Operating temperature:-40°C to+105°C  
Soldering temperature:+255°C

X5621 W V-2\*XX-C762 D1196-1196



- ① Series.N0.
- ② Category : W-Wafer
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:2\*XX-03,04,05,06,07,08,09,10,12,14,16 20,21,24,25
- ⑤ Plastic Height :C=7.62mm
- ⑥ Pin Length :D:1196=11.96mm;1000=10.0mm;1220=12.20mm;
- ⑦ 1196-Type1196

|                             |           |                    |                  |                           |
|-----------------------------|-----------|--------------------|------------------|---------------------------|
| X5621WV-2*XX-C762D1196-1196 | PPS 94V-0 | Brass              | Tin<br>Gold 1u"  | X5621F                    |
| PART NO                     | Material  | Material(Terminal) | Finish(Terminal) | Mates With XKB Pin Header |

广东星坤科技股份有限公司

| 生     | 日期 |
|-------|----|
| 發     | 日期 |
| ΔX    |    |
| MARK  |    |
| 文件工程章 |    |

REVISIONS

www.xk-ig.cn www.helloxkb.com www.helloxkb.cn

|             |      |
|-------------|------|
| ANGLAR      | ±5°  |
| L ≤ 4       | ±0.2 |
| 4 < L ≤ 16  | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63      | ±0.5 |

UNSPECIFIED TOLERANCES

|                                      |      |             |                             |
|--------------------------------------|------|-------------|-----------------------------|
| DSND                                 | DATE | SCALE: N/A  | MODEL TYPE:                 |
| DWN                                  | DATE | VIEW:       | PART NO.:                   |
| CHKD                                 | DATE | UNIT: mm/in | DWG NO.:                    |
| APPD                                 | DATE | SIZE: A4    | X5621WV-2*XX-C762D1196-1196 |
| KKB INDUSTRIAL PRECISION CO.,LIMITED |      |             | WEIGHT                      |
|                                      |      |             | SHEET                       |
|                                      |      |             | REVISION                    |
|                                      |      |             | 1.0g                        |
|                                      |      |             | 1/1                         |
|                                      |      |             | A0                          |