



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 7A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 1000M \Omega$
- Contact resistance:  $\leq 10m\Omega$
- After environmental testing :  $\leq 20m\Omega$

X8672 H X- XX A -N2 XX



- ① Series No
- ② Category:  
H-HSG
- ③ Welding Board Angle:  
Blank-Ordinary
- ④ Row No.-Pin No.:  
XX-Single Row
- ⑤ Special No:  
A-Flat on both sides
- ⑥ Material:  
N2-PA66 94V-2
- ⑦ Color:  
Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		BA	BA
2	3.96	8.43	12	43.56	48.03
3	7.92	12.39	13	47.52	51.99
4	11.88	16.35	14	51.48	55.95
5	15.84	20.31	15	55.44	59.91
6	19.80	24.27	16	59.40	63.87
7	23.76	28.23	17	63.36	67.83
8	27.72	32.19	18	67.32	71.79
9	31.68	36.15	19	71.28	75.75
10	35.64	40.11	20	75.24	79.71
11	39.60	44.07			

X8672H-XXA-N2	Nylon 66 UL 94V-2	X8672T	X8672W	1,000Pcs
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal	Q'ty/Bag

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X8672H-XXA-N2
DWN	DATE	VIEW:	PART NO.: 3.96mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn