






XKB




X9357 W R X 2 XX SX XX SN XX

- 01 Series No.
- 02 Category:W-wafer
- 03 Welding Board Angle:R-90°
- 04 Welding Way: Blank-DIP;
- 05 Row No.-Pin No.: 2*XX-Double row
- 06 Special NO.
- 07-With positioning column F-halogen free
- 07 Material:NO-PA6694V-0;N2-PA6694V-2 LP-LCP 94V-0
- 08 Planting Category: SN-Bright tin plating 70u"
- 09 Color: Blank-natural color
BK-BLACKBL-BLUE RE-RED

Specifications:

规格: XKB
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃+85℃
温度范围: -25℃+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤30mΩ
After environmental test:≤20mΩ
环境测试后: ≤20兆欧

Poles	Dimensions(mm)	
	A	B
2*01	---	5.40
2*02	4.20	9.60
2*03	8.40	13.80
2*04	12.60	18.00
2*05	16.80	22.20
2*06	21.00	26.40
2*07	25.20	30.60
2*08	29.40	34.80
2*09	33.60	39.00
2*10	37.80	43.20
2*11	42.00	47.40
2*12	46.20	51.60



X9357WR-2* XXS-LPSN	LCP UL 94V-0	Brass	Tin- Plated	X9357H
X9357WR-2*XXSF-NOSNBK	Nylon 66 UL 94V-0 Halogen Free			
X9357WR-2*XXS-N0SNXX	Nylon 66 UL 94V-0			
X9357WR-2* XXS-N2SNXX	Nylon 66 UL 94V-2			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司
生 日期
文件工程章
REVISIONS
www.heloxkb.com

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.: 2.40mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0