






XKB



## Specifications:

规格: XKB  
**Voltage rating:** 600V AC/DC  
**额定电压:** 600V AC/DC  
**Current rating:** 9A AC/DC  
**额定电流:** 9A AC/DC  
**Withstanding voltage:** 1500V AC/minute  
**耐受电压:** 1500V AC/分钟  
**Temperature range:** -25°C +85°C  
**温度范围:** -25°C +85°C  
**Insulation resistance:** ≥1000MΩ  
**绝缘电阻:** ≥1000MΩ  
**Contact resistance:** ≤10mΩ  
**接触电阻:** ≤10mΩ  
**After environmental testing:** ≤20mΩ  
**环境测试后:** ≤20mΩ

X9357 W V X-2\*XX X-XX SN XX  
 ○ ○ ○ ○ ○ ○ ○ ○ ○ ○

- 01 Series No.  
 02 Category W-wafer  
 03 Weiding Board Angle: V-180°  
 04 Weiding Way: Blank-DIP  
 05 Row No. -Pin No: 2\*xx-Double row  
 06 Special NO.  
 B-Arrange ushering with positioning column  
 07 Material NO-PA66 94V-0/N2-PA66 94V-2  
 08 Plating Category  
 V All Gold-Plated G Gold-Plated Contact  
 S-Silver Plating, \*01-G-old Flash, \*02-2u", \*03-3u"  
 \*05-5u", \*10-10u", \*15-15u", \*30-30u", \*50-50u"  
 N-Plating Nickel 30u", SN-Bright tin plating 70u" SW-F5  
 Tin plating  
 09 Color Blank-natural color

Poles	Dimensions(mm)	
	A	B
2*07	25.20	40.00
2*08	33.60	48.40
2*09	46.20	61.00

X9357WV-2*XKB-N0SN	Nylon 66 UL 94V-0	Phorpos Bronze	Tin-Plated	X9357HM-B
X9357WV-2*XKB-N2SN	Nylon 66 UL 94V-2	Phorpos Bronze	Tin-Plated	X9357HM-B
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

www.heloxkb.com

DATE	REVISED	APPROVED	DESCRIPTION

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	X9357WV-2*XXB-N0SN
CHKD	DATE	UNIT: mm/in	PART NO.: 4.20 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0