



SECTION A-A
SCALE 1:1

Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
After environmental testing:≤30mΩ
环境测试: ≤30兆欧

X9555 H X-2xXX A-PTXX

① ②③ ④ ⑤⑥ ⑦

- 1.Series No
- 2.Category:H-HSG
- 3.Welding Board Angle:Blank-ordinary
- 4.Row No-Pin No:2xXX-2x02P~2x32P
- 5.Special No:A-Single convex(HTS 2.54)
- 6.Material:PT-PBT 94V-0
- 7.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B		A	B
2x02	2.54	9.48	2x13	30.48	37.42	2x24	58.42	65.36
2x03	5.08	12.02	2x14	33.02	39.96	2x25	60.96	67.90
2x04	7.62	14.56	2x15	35.56	42.50	2x26	63.50	70.44
2x05	10.16	17.10	2x16	38.10	45.04	2x27	66.04	72.98
2x06	12.70	19.64	2x17	40.64	47.58	2x28	68.58	75.52
2x07	15.24	22.18	2x18	43.18	50.12	2x29	71.12	78.06
2x08	17.78	24.72	2x19	45.72	52.66	2x30	73.66	80.60
2x09	20.32	27.26	2x20	48.26	55.20	2x31	76.20	83.14
2x10	22.86	29.80	2x21	50.80	57.74	2x32	78.74	85.68
2x11	25.40	32.34	2x22	53.34	60.28			
2x12	27.94	34.88	2x23	55.88	62.82			

X9555H-2xXXA-PT	PBT UL 94V-0	X955T	X9555W
PART NO	Material	Material(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期					units: mm
ΔX						tolerance:
ΔX						X.X ±0.2mm
ΔX						X.XX ±0.1mm
MARK						X.XXX ±0.05mm
文件工程章	DESCRIPTION	DATE	REVISED	APPROVED		UNSPECIFIED TOLERANCES
	REVISIONS					
	www.xk-dg.cn	www.helloxkb.com	www.helloxkb.cn			

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	2.00mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED					X9555H-2xXXA-PT
	WEIGHT	SHEET	REVISION		
	1.0g	1/1	A0		