


Dim(L)	E1=2.50
	E=2.90



Specifications:

规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating:3A AC/DC
 额定电流: 3A AC/DC
Withstanding voltage:1500V AC/minute
 耐受电压: 1500V AC/分钟
Temperature range:-25°C~+85°C
 温度范围: -25°C~+85°C
Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧

X9555 W V XX-2xXX EX- PT V01 XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- Series No
- Category:W-WAFER
- Welding Board Angle:V-180°
- Welding Way:S-SMT
- Row No-Pin No:2xXX-Double Row
- Special NO:
E-Matching 9555H-2xXXE HSG,DIP-2.90mm
E1-DIP-2.50mm
- Material:PT-PBT 94V-0
- Plating Category:V01-Gold Flash
SN-Bright Tin Plating(70u")
- Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	5.08	10.12	8.12	2x12	27.94	32.98	30.98
2x04	7.62	12.66	10.66	2x13	30.48	35.52	33.52
2x05	10.16	15.20	13.20	2x14	33.02	38.06	36.06
2x06	12.70	17.74	15.74	2x15	35.56	40.60	38.60
2x07	15.24	14.00	18.28	2x16	38.10	43.14	41.15
2x08	17.78	20.28	20.82	2x17	40.64	45.68	43.68
2x09	20.32	25.36	23.36	2x18	43.18	48.22	46.22
2x10	22.86	27.90	25.90	2x19	45.72	50.76	48.76
2x11	25.40	30.44	28.44	2x20	48.26	53.30	51.30

X9555WV-2xXXE1-P TV01	PBT UL 94V-0	Brass	Gold-Flash	X9555H-E
X9555WVS-2xXXE-P TV01	PBT UL 94V-0		Gold-Flash	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
ΔX	ΔX
ΔX	ΔX
MARK	文件工程章

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm
UNSPECIFIED TOLERANCES	

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X9555WVS-2xXXEX-PTV01
APPD	DATE	SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0