



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1500V AC/minute
 耐受电压: 1500V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧

X9555 W R S-2xXX X-6T V01 XX

- ① ②③④ ⑤ ⑥⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-wafer
- 3.Welding Board Angle:V-180°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:2xXX-Double row
- 6.Special No:
- 7.Material:6T-PA6T 94V-0
- 8.Planting Category:VXX:All Gold-Plated X01-Gold Flash
- 9.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x02	2.54	12.58	10.28	2x12	27.94	37.98	35.68
2x03	5.08	15.12	12.82	2x13	30.50	40.52	38.22
2x05	10.16	20.20	17.90	2x15	35.56	45.60	43.30
2x06	12.70	22.74	22.44	2x17	40.64	50.68	48.38
2x07	15.24	25.28	22.98	2x20	48.26	58.30	56.00
2x08	17.78	27.82	25.52	2x25	60.86	71.00	68.70
2x09	20.32	30.36	28.06	2x30	73.70	83.70	81.40
2x10	22.86	32.90	30.60	2x32	78.74	88.78	86.48

X9555WVS-2xXX-6TV01	Nylon6T UL 94V-0	Brass	Gold-Flash	X9555H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

Recommended PCB Layout
 General Tolerance±0.05

广东星坤科技股份有限公司

生	日期
效	
效	
效	
MARK	文件工程章

DATE	REVISED	APPROVED	units: mm
			tolerance:
			X.X ±0.2mm
			X.XX ±0.1mm
			X.XXX ±0.05mm
			UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X9555WVS-2xXX-6TV01
APPD	DATE	SIZE: A4	WEIGHT 1.0g
KKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0