




RATING	0.5A 12V DC
CIRCUIT	2P4T
CONTACT RESISTANCE	100m MAX
TRAVEL	2mm
OPERATING FORCE	200±100gf
OPERATING LIFE(cycles)	10 000




PCB Position and Size



PAPT NO	L
SS-3456S-02-L1	2.0
SS-3456S-02-L2	3.0
SS-3456S-02-L3	4.0



The circuit principle diagram



ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK
4	Terminal	4	4	Phosphor copper	ag Plated	
3	Base	1	1	LCP		
2	Cover	1	1	Sus	Natural	
1	Keystake	1	1	Pa66	Black	

广东星坤科技股份有限公司

生	日期
ΔX	日期
ΔX	日期
ΔX	日期
MARK	文件工程章

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: SS-3456S-02-X
APPD		DATE		SIZE: A4	
KKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT: 1.0g
					SHEET: 1/1
					REVISION: A0