




XKB






4P-25P




3P



2P



3P~25P



02P

Specificationsxkb

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC XKB

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ XKB

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X9556 H F-XX X-PT XX

① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category : H-HS G

③ Welding Board Angle : F-Fmale HGS

④ Row No.-Pin No.: XX-Single row

⑤ Special No.

⑥ Material : PT-PBT 94V-0

⑦ Color : Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B		A	B
02	2.54	7.12	10	22.86	27.44	18	43.18	47.76
03	5.08	9.66	11	25.40	29.98	19	45.72	50.30
04	7.62	12.20	12	27.94	32.52	20	48.26	52.84
05	10.16	14.74	13	30.48	35.06	21	50.08	55.38
06	12.70	17.28	14	33.02	37.60	22	53.34	57.92
07	15.24	19.82	15	35.56	40.14	23	55.88	60.46
08	17.78	22.36	16	38.10	42.68	24	58.42	63.00
09	20.32	24.90	17	40.64	45.22	25	60.96	65.54

X9556H-F-XX-PT	FBT UL 94V-0	X9556TM	X9556H
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	X9556HF-XX-PT
CHKD	DATE	UNIT: mm/in	PART NO.: 2.54 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0