


SECTION A-A
SCALE 1:1



SECTION B-B
SCALE 1:1

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X9556 T M-B S N

① ② ③ ④ ⑤ ⑥ ⑦

① Series Number

② Category: T-terminal

③ Shape:M-male

④ Material:Brass

⑤ Plating style:SN-Bright tin plating

广东星坤科技股份有限公司

生
效

日
期

Δ

MARK

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

XKB

ANGLAR

±5°

15 4 ±0.2

4<15 16 ±0.3

16<15 63 ±0.4

15<63 ±0.5

X9556 T M-B S N	Brass	AIR 0422-28	1.63mm(Max)	Stamping Before Plating:30W Ni70u3Sn	X9556H
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	X9556TM-BSN
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT 1.0g	SHEET 1/1
					REVISION A0