




MODEL CODE



Typical Specifications

- 1.Rating:AC 125V 3A
- 2.Insulation Resistance:1,000M min
- 3.Dielectric strength:1,500V RMS
- 4.Operating Life: 10,000 cycles

ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	3	Copper Alloy	silver plated	——
④	Contact	—	1	Copper Alloy	silver plated	——
③	Housing	—	1	Stainless Steel		——
②	Slide Handle	—	1	Nylon		——
①	Case	—	1	Diallyl Phthalate (DAP)		——

广东星坤科技股份有限公司

生效	日期
ΔX	
ΔX	
ΔX	
MARK	

DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	SLIDE SWITCH
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.: SS-12D28XX
			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.helloxb.com www.helloxb.com www.helloxb.com

XKB INDUSTRIAL PRECISION CO., LIMITED