



SCHMATIC

SS13F24- X  
L(MM)  
2 ~ 10



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISITANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

广东星坤科技股份有限公司

生	ΔX	日期
效	ΔX	日期
ΔX		
MARK		

DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN		DATE		VIEW:	PART NO.: SS13F24
CHKD		DATE		UNIT: mm/in	DWG NO.: SS13F24X
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

文件工程章

REVISIONS  
[www.hellokd.cn](http://www.hellokd.cn) [www.helloxb.com](http://www.helloxb.com) [www.helloxb.cn](http://www.helloxb.cn)

UNSPECIFIED TOLERANCES

units: mm  
 tolerance:  
 X.X ±0.2mm  
 X.XX ±0.1mm  
 X.XXX ±0.05mm

DATE REVISED APPROVED

DESCRIPTION