




03P~30P Double Salient



02P Single Salient

Scale 1:2



■ Specifications :

- Voltage rating: 150V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥500MΩ
- Contact resistance: ≤30mΩ
- After environmental testing : ≤40mΩ

X9862 H-XX-N0 HF

- ① Series No.
- ② Category : H-HSG
- ③ Row No.-Pin No.: XX-02P~30P
- ④ Material : N0-PA66 94V-0
- ⑤ HF-Halogen Free

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.25	4.35	2.85	11	12.50	15.60	14.10
03	2.50	5.60	4.10	12	13.75	16.85	15.35
04	3.75	6.85	5.35	13	15.00	18.10	16.60
05	5.00	8.10	6.60	14	16.25	19.35	17.85
06	6.25	9.35	7.85	15	17.50	20.60	19.10
07	7.50	10.60	9.10	20	23.75	26.85	20.35
08	8.75	11.85	10.35	25	30.00	33.10	31.60
09	10.00	13.10	11.60	30	36.25	39.35	37.85
10	11.25	14.35	12.85				

X9862H-XX-N0HF	PA66 UL 94V-0 Halogen Free	X9862T	X9862W
X9862H-XX-N0	PA66 UL 94V-0		
PART NO	Material	Suitable X KB Terminal	Suitable X KB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X9862H-XX-N0XX
DWN	DATE	VIEW:	PART NO.: 1.25mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章