



Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-001-D6-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-001-D6-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-001-D6-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-001-D6-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-001-D6-05	DC5V	20mA	20mA	1.9V	2.4V

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑦	LED		1			
⑥	Hat		1	ABS		
⑤	Terminal	—	4	Brass (0.30t)	ag Plated	—
④	Contact	—	1	F.ag/SUS		—
③	Base	—	1	PA66		—
②	Cover	—	1	PA66		—
①	Keystake	—	1	PA66		—

广东星坤科技股份有限公司

生	日期
教	
文件	工程
章	

DATE	REVISED	APPROVED	units: mm
			tolerance:
			X.X ±0.2mm
			X.XX ±0.1mm
			X.XXX ±0.05mm

DSND	DATE	SCALE: N/A	MODEL TYPE: LED SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: TM-001-D6-X
APPD	DATE	SIZE: A4	WEIGHT: 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET: 1/1
			REVISION: A0