



Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-001-M-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-001-M-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-001-M-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-001-M-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-001-M-05	DC5V	20mA	20mA	1.9V	2.4V

⑦	LED		1			
⑥	Hat		1	ABS		
⑤	Terminal	—	4	Brass (0.30t)	ag Plated	—
④	Contact	—	1	F.ag/SUS		—
③	Base	—	1	PA66		—
②	Cover	—	1	PA66		—
①	Keystake	—	1	PA66		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

广东星坤科技股份有限公司

生 日期  
教 日期

文件工程章

DESCRIPTION

DATE

REVISED

APPROVED

REVISIONS

UNSPECIFIED TOLERANCES

units: mm

tolerance:

X.X ±0.2mm

X.XX ±0.1mm

X.XXX ±0.05mm

DSND

DATE

SCALE: N/A

MODEL TYPE:

LED SWITCH

DWN

DATE

VIEW:

PART NO.:

CHKD

DATE

UNIT: mm/in

DWG NO.:

TM-001-M-X

APPD

DATE

SIZE: A4

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT

SHEET

REVISION

1.0g

1/1

A0