



Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-002-M-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-002-M-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-002-M-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-002-M-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-002-M-05	DC5V	20mA	20mA	1.9V	2.4V

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑦	LED		1			
⑥	Hat		1	ABS		
⑤	Terminal		4	Brass (0.30t)	ag Plated	
④	Contact		1	F.ag/SUS		
③	Base		1	PPA		
②	Cover		1	PPA		
①	Keystake		1	PPA		

广东星坤科技股份有限公司

生 日期
教 日期

文件工程章

DESCRIPTION

DATE

REVISED

APPROVED

REVISIONS

UNSPECIFIED TOLERANCES

units: mm

tolerance:

X.X ±0.2mm

X.XX ±0.1mm

X.XXX ±0.05mm

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	LED SWITCH
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.: TM-002-M-X
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0