



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 40±10gf
 Lifetime: 100,000 Cycles

PART NO	H
TM-W07A-1	8.3
TM-W07A-2	8.5
TM-W07A-3	8.7
TM-W07A-4	9.3
TM-W07A-5	11.0
TM-W07A-6	12.3
TM-W07A-7	13.7

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Plating silver	—
④	Terminal	—	4	Phosphor Bronze	Plating silver	—
③	Base	—	1	Nylon		—
②	Cover	—	1	Nylon		—
①	Keystake	—	1	Nylon		—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	units: mm	tolerance:	DSND	DATE	SCALE: N/A	MODEL TYPE: DETECT SWITCH
ΔX							DWN	DATE	VIEW:	PART NO.:
ΔX					X.X ±0.2mm		CHKD	DATE	UNIT: mm/in	DWG NO.: TM-W07A-X
ΔX					X.XX ±0.1mm		APPD	DATE	SIZE: A4	
					X.XXX ±0.05mm					
					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
										SHEET 1/1
										REVISION A0