






XKB



P.C.B LAYOUT



Specificationsxkb

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC xkb
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25°C+85°C
 温度范围: -25°C+85°C
 Insulation resistance:≥500MΩ
 绝缘电阻: ≥500MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ xkb
 After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧

X8821 WR X-XX SL-NO SN
 ○○○○○○ ○○○○○○

- Series No.
- Category:W-WAFER
- Welding Board Angle: R-Right Angle 90°
- Welding Wway:Blank-DIP
- Row No.Pin No.: XX-Single Row;
- Plug the Pin&Special No.:
 s-Without Positioning;L-With Lock
- Material: NO-PA66 94V-0
- Plating Category: SN-Bright Tin Plating

Circuits	Dimension mm			Circuits	Dimension mm		
	A	B	C		A	B	C
2	2.50	7.50	6.00	10	22.50	27.50	26.00
3	5.00	10.00	8.50	11	25.00	30.00	28.50
4	7.50	12.50	11.00	12	27.50	32.50	31.00
5	10.00	15.00	13.50	13	30.00	35.00	33.50
6	12.50	17.50	16.00	14	32.50	37.50	36.00
7	15.00	20.00	18.50	15	35.00	40.00	38.50
8	17.50	22.50	21.00				
9	20.00	25.00	23.50				

广东星坤科技股份有限公司

生 日期
 發

文件工程章

REVISIONS
 www.helxkb.com

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	X8821WR-XXSL-NO5N
CHKD	DATE	UNIT: mm/mn	PART NO.: 2.50mm Crimp Style Connector
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0

X8821WR-XXSL-NO5N	Nylon 66 UL 94V-0	Brass	Tin-Plated	X8821H-L
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing