



ITEM	PART NAME	TER. NO	QTY	MATERIAL	FINISHING	REMARK
④	Terminal	6		Brass (0.30t)	ag Plated	
③	Base	1		Phenolic Resin		
②	Cover	1		Sus	Natural	
①	Keystake	1		Pa66	Black	

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(CYCLES)	10,000

广东星坤科技股份有限公司

生效日期

文件工程章

DSND	DATE	SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN	DATE	VIEW:	PART NO.: SK14D07
CHKD	DATE	UNIT: mm/in	DWG NO.: SK14D07XX
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

REVISIONS  
 www.xk-d.com www.helloxkb.com www.helloxkb.cn

UNSPECIFIED TOLERANCES