




RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100m MAX
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(cycles)	10 000



ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING
4	Terminal	—	6	Brass (0.30t)	ag Plated
3	Base	—	1	Phenolic Resin	
2	Cover	—	1	Sus	Natural
1	Keystake	—	1	Pa66	Black

广东星坤科技股份有限公司

生	日期
效	
MARK	文件工程章

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A
DWN		DATE		VIEW:
CHKD		DATE		UNIT: mm/in
APPD		DATE		SIZE: A4

MODEL TYPE:	SLIDE SWITCH		
PART NO.:			
DWG NO.:	SS14D07XX		
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	

XKB INDUSTRIAL PRECISION CO., LIMITED