



PCB LAYOUT



■ Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing : ≤40mΩ

X1511 W V S-XX HF-LP SW
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No. : XX-02P~15P
- ⑥ Plug the Pin & Special NO.:HF-Halogen free
- ⑦ Material : 9T-PA9T;46-PA46;LP-LCP 94V-0
- ⑧ Planting Category:SW-Matte Tin Plating

| Poles | Dimensions(mm) | | |
|-------|----------------|-------|-------|
| | A | B | C |
| 02 | 1.50 | 4.30 | 3.70 |
| 03 | 3.00 | 5.80 | 5.20 |
| 04 | 4.50 | 7.30 | 6.70 |
| 05 | 6.00 | 8.80 | 8.20 |
| 06 | 7.50 | 10.30 | 9.70 |
| 07 | 9.00 | 11.80 | 11.20 |
| 08 | 10.50 | 13.30 | 12.70 |
| 09 | 12.00 | 14.80 | 14.20 |
| 10 | 13.50 | 16.30 | 15.70 |
| 11 | 15.00 | 17.80 | 17.20 |
| 12 | 16.50 | 19.30 | 18.70 |
| 13 | 18.00 | 20.80 | 20.20 |
| 14 | 19.50 | 22.30 | 21.70 |
| 15 | 21.00 | 23.80 | 23.20 |

| | | | | |
|--------------------|---------------------------|--------------------------|-------------------|------------------------|
| X1511WS-XXHF-LP SW | LCP UL 94V-0 Halogen Free | Brass | Matte Tin Plating | X1511H |
| PART NO | Material | Material(Pin&Solder Tab) | Finish(Pin) | Suitable XKGB Terminal |

广东星坤科技股份有限公司

生效

| | |
|------|-------------|
| ΔX | 日期 |
| ΔX | |
| ΔX | |
| MARK | DESCRIPTION |

| REVISIONS | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------|------|---------|----------|------------------------|
| | | | | |

| | | | |
|---------------------------------------|------|-------------|--|
| DSND | DATE | SCALE: N/A | MODEL TYPE: X1511VWS-XXHF-XXSW |
| DWN | DATE | VIEW: ④ | PART NO.: 1.5mm Crimp Style Connectors |
| CHKD | DATE | UNIT: mm/in | DWG NO.: |
| APPD | DATE | SIZE: A4 | |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | | WEIGHT: 1.0g |
| | | | SHEET: 1/1 |
| | | | REVISION: A0 |

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn