



**Specifications:**

规格:  
**Voltage rating:**250V AC/DC  
 额定电压: 250V AC/DC  
**Current rating:**3A AC/DC  
 额定电流: 3A AC/DC  
**Withstanding voltage:**800V AC/minute  
 耐受电压: 800V AC/分钟  
**Temperature range:**-25°C~+85°C  
 温度范围: -25°C~+85°C  
**Insulation resistance:**≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
**Contact resistance:**≤10mΩ  
 接触电阻: ≤10mΩ  
**After environmental testing:**≤20mΩ  
 环境测试后: ≤20兆欧

**X2026 W V X-2xXXX-NOXXXXX**

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:Blank-DIP
- 5.Row No-Pin No:2xXX-2x02P~2x22P
- 6.Plug the Pin&Special NO:HF-Halogen Free
- 7.Material:N0-PA66 94V-0
- 8.Plating Category:SN-Bright Tin Plating  
V01-All Gold Flash
- 9.Color:Blank-Natural Color; BK-Black;WH-White

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	6.00	4.80	2x09	16.00	20.00	18.80	2x16	30.00	34.00	32.80
2x03	4.00	8.00	6.80	2x10	18.00	22.00	20.80	2x17	32.00	36.00	34.80
2x04	6.00	10.00	8.80	2x11	20.00	24.00	22.80	2x18	34.00	38.00	36.80
2x05	8.00	12.00	10.80	2x12	22.00	26.00	24.80	2x19	36.00	40.00	38.80
2x06	10.00	14.00	12.80	2x13	24.00	28.00	26.80	2x20	38.00	42.00	40.80
2x07	12.00	16.00	14.80	2x14	26.00	30.00	28.80	2x21	40.00	44.00	42.80
2x08	14.00	18.00	16.80	2x15	28.00	32.00	30.80	2x22	42.00	46.00	44.80

X2026WV-2xXXHF-NOSNBK	PA66 UL 94V-0 Black(Halogen Free)	Brass	Tin-Plated	X2026H
X2026WV-2xXX-N0 SNWH	PA66 UL 94V-0 White		Tin-Plated	
X2026WV-2xXX-N0 V01	PA66 UL 94V-0		Gold-Flash	
X2026WV-2xXX-N0 SN			Tin-Plated	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司  
 Recommended PCB Layout  
 General Tolerance:±0.05

生	日期
效	
文件	工程
MARK	章

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A
DWN	DATE	VIEW:
CHKD	DATE	UNIT: mm/in
APPD	DATE	SIZE: A4
KKB INDUSTRIAL PRECISION CO., LIMITED		

MODEL TYPE: Wire to board connector		
PART NO.: 2.00mm Crimp Style Connectors		
DWG NO.: X2026WV-2xXX-N0XXX		
WEIGHT 1.0g	SHEET 1/1	REVISION A0