



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω

X3025 W V X-2*XX X-XX XX XX
 ○ ○ ○ ○ ○ ○ ○ ○

- Series No.
- Category : W-WAFER
- Welding Board Angle : V-Stright 180°
- Welding Way : Blank-DIP
- Row No.-Pin No. : 2*XX-2*01P-2*22P
- Plug the Pin & Special No.:
- Material: 66-PA66 94V-0 ;PT-PBT 94V-0; 46-PA46 94V-0 LP-LCP 94V-0
- Plating Category: SN-Bright Tin Plating; V01-All Gold Flash
- Color : Blank-Natural Color

X3025 WV-2*XX-46V01	PA46 UL 94V-0	Brass	Gold-Flash	X3025H
X3025 WV-2*XX-LPSN	LCP UL 94V-0		Tin-Plated	
X025 WV-2*XX-66JN	PA66 UL 94V-0	Flash(Pin)	Mate s With XK B Housing	
X3025 WV-2*XX-46SN	PA46 UL 94V-0			
X3025 WV-2*XX-PTSN	PBT UL 94V-0			

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	---	6.65	2*07	18.00	24.65
2*02	3.00	9.65	2*08	21.00	27.65
2*03	6.00	12.65	2*09	24.00	30.65
2*04	9.00	15.65	2*10	27.00	33.65
2*05	12.00	18.65	2*11	30.00	36.65
2*06	15.00	21.65	2*12	33.00	39.65

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

www.helxkb.com

XKB	ANGLAR	±5°
	L ≤ 4	±0.2
	4 < L ≤ 16	±0.3
	16 < L ≤ 63	±0.4
	L > 63	±0.5
UNSPECIFIED TOLERANCES		

DSND	DATE	SCALE: NA	MODEL TYPE: X3025WV-2*XX-XXXX
DWVN	DATE	VIEW:	PART NO.: 3.00 mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0