




PROPOSAL DRAWING

RECOMMENDED P.C.B LAYOUT (THICKNESS=1.2mm)
(COMPONENT SIDE) P.C.B TOLERANCE ±0.05

Housing Material: PA9T UL94V-0, Black
Contact Terminal: PHOSPHOR BRONZE (t=0.25mm).
Metallic Shell: Brass(t=0.30mm).



U221-04XN-3BU01-X5

- 1-Au 1U"
- 5-Au 15U"
- 6-Au 30U"
- 1-PBT
- 2-PA6T
- 3-PA6T
- 4-LCP
- 5-BRASS
- S-Scrolls F Flat
- W-WHITE B-BLACK

广东星坤科技股份有限公司

生 日期
蔡




文件工程章
REVISIONS

DATE REVISED APPROVED
www.xkpcb.com www.hellxkb.com

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES




DSND	DATE	SCALE: N/A	MODEL TYPE: USB 2.0
DWNT	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: U221-04XN-3BU01-S5
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1.0g 1/1 A0



PROPOSAL DRAWING

RECOMMENDED P.C.B LAYOUT (THICKNESS=1.2mm)
(COMPONENT SIDE) P.C.B TOLERANCE: ±0.05

Housing Material: PA9T UL94V-0, Black
Contact Terminal: PHOSPHOR BRONZE (t=0.25mm).
Metallic Shell: Brass(t=0.30mm).



U221-04XN-3BU01-X5

- 1 Au 1U"
- 5 Au 15U"
- 6 Au 30U"
- 1 PBT
- 2 PA6T
- 3 PA9T
- 4 LCP
- 5 BRASS
- S Scrolls F Flat
- W/WHITE B BLACK

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

ANGLAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: USB 2.0
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: U221-04XN-3BU01-F5
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION 1.0g 1/1 A0
XKB INDUSTRIAL PRECISION CO., LIMITED			