



RECOMMENDED P.C.B LAYOUT (COMPONENT SIDE)
 DEFAULT TOLERANCES: ±0.05; PCB THICKNESS: 1.2mm

Housing Material: LCP UL94V-0, black
 Contact Terminal: Brass
 Metallic Shell: SUS



U221-04XN-4BU05-FS

- S: SUS
- F: Flat
- W: WHITE B: BLACK

1: Au 1U"
 5: Au 15U"
 6: Au 30U"

1: PBT
 2: PA6T
 3: PA9T
 4: LCP

						DSND		DATE		SCALE: N/A	MODEL TYPE: USB 2.0	
ΔX						DWN		DATE		VIEW:	PART NO.:	
Δx						CHKD		DATE		UNIT: mm/in	DWG NO.:	
Δx						APPD		DATE		SIZE: A4	U221-04XN-4BU05-FS	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION
						XKB INDUSTRIAL PRECISION CO., LIMITED				1.0g	1/1	A0