


■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1.5A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ

X1011 W R S- XX- XX V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:W-WAFER
- ③ Wedding Board Angle : R-Right 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.:XX-04P~07P
- ⑥ Material:LP-LCP 94V-0;4T-PA4T
- ⑦ Planting Category:V01-All Gold Flash

Poles	Dimensuons(mm)		
	A	B	C
02	1.20	4.20	2.65
03	2.40	5.40	3.85
04	3.60	6.60	5.05
05	4.80	7.80	6.25
06	6.00	9.00	7.45
07	7.20	10.20	8.65
10	10.80	13.80	12.25



X1224WRS-XX-4TV01	PA4T UL 94V-0	Phosphor Bronze	Gold-Flash	X1224H
X1224WRS-XX-LPV01	LCP UL 94V-0	Phosphor Bronze	Gold-Flash	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE: X1224WRS-XX-XXV01
DWN	DATE	VIEW:	PART NO.: 1.20mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

ΔX					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						