




Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤30mΩ
 接触电阻: ≤30mΩ
 After environmental testing:≤40mΩ
 环境测试后: ≤40兆欧

X2011 W R X-XX A HF-N0 SN XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:R-Right Angle 90°
- 4.Welding Way:Blank-DIP
- 5.Row No-Pin No:XX-02P~16P
- 6.Plug the Pin&Special NO:
A-With Link Stopper DIP-3.2mm
- 7.HF-Halogen Free
- 8.Material:N0-PA66 UL 94V-0
- 9.Plating Category:SN-Bright Tin Plating
- 10.Color:Blank-Natural Color



poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2	2.00	8.00	4.70	10	18.00	22.00	20.70
3	4.00	10.00	6.70	11	20.00	24.00	22.70
4	6.00	12.00	8.70	12	22.00	26.00	24.70
5	8.00	14.00	10.70	13	24.00	28.00	26.70
6	10.00	16.00	12.70	14	26.00	30.00	28.70
7	12.00	18.00	14.70	15	28.00	32.00	30.70
8	14.00	20.00	16.70	16	30.00	34.00	32.70
9	16.00	22.00	18.70				

X2011WR-XXAHF-N0 SN	PA66 UL 94V-0 Halogen Free	Brass	Tin-Plated	X2011H
X2011WR-XXA-N0SN	PA66 UL 94V-0			
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司
 Recommended PCB Layout
 General Tolerance:±0.05

生	日期	DESCRIPTION	DATE	REVISED	APPROVED	units:	mm
ΔX						tolerance:	
ΔX						X.X	±0.2mm
ΔX						X.XX	±0.1mm
MARK						X.XXX	±0.05mm
文件工程章						UNSPECIFIED TOLERANCES	
REVISIONS						www.xk-dg.cn www.helloxkb.com www.helloxkb.cn	

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.: 2.00mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.: X2011WR-XXA-N0SN
APPD		DATE		SIZE: A4	WEIGHT 1.0g
KKB INDUSTRIAL PRECISION CO., LIMITED					SHEET 1/1
					REVISION A0